




Case History

Customer: *Requested to Remain Confidential*

Location: *McPherson, Kansas*

Machine: *F329 - 10*

Application: *This machine is being used in conjunction with other equipment, giving the F329 a signal to dispense product into .35 to 5.3 ml dental cartridges at speeds up to 20 cycles per minute.*



F329 Features

- Fills Aqueous to Light Oil Products
- Up to 30 ml Fills
- 2 Quintuplex Valve Assemblies
- Exclusive Patented, Slide-Type Valve

This long-term Cozzoli customer has several old machines designed to fill carpules also known as dental cartridges. Their equipment used peristaltic pumps, which were not accurate. This customer decided to put the F329 in line to increase their fill accuracies.



Case History, Continued



Tim & Chip: Happy Cozzoli Customers!

Special Features Include:

- **Stainless Steel Exterior**
- **Electronic Fill Volume Adjustment**
- **Individual Fine Fill Adjustment of Each Pump**

Easy to Operate Controls

Easy Volumetric Adjustments: This machine has an electronically driven volume selector for simple adjustment –

Takes only Seconds!



For more information on this filler, contact the Cozzoli Machine Company Sales Department phone: 732-564-0400, fax 732-564-0444, email sales@cozzoli.com, or visit our website: www.cozzoli.com.